

Fraunhofer

TESTED® DEVICE

Lindner AG Crono-I Clean 625 TW NL **Report No. LI 1809-1068**

Statement of Qualification

Particle Emission





Statement of Qualification

Lindner AG Customer

> Moosstrasse 1 84051 Mettenbach

Germany

Component tested

Cleanroom Facilities Category:

Lighting Systems Subcategory

Product name: Recessed luminaireCrono-I Clean 625 TW NL

(manufacturing date: 6/19/2018; color: RAL 9016;

serial number: IP18/008606)

Random sampling of particle emissions (airborne) at representative sites

Standards/Guidelines:

ISO 14644-1. -14

The norms stated generally refer to the version valid at the time of the tests.

Test devices:

Optical particle counter:

LasAir II 110 and LasAir III 110 with measuring ranges $\geq 0.1 \,\mu\text{m}$, $\geq 0.2 \,\mu\text{m}$, \geq 0.3 μ m, \geq 0.5 μ m, \geq 1.0 μ m and \geq 5.0 μ m

Test environment parameters:

Airflow pattern:.....vertical laminar flow

• Relative humidity: 45 % ±5 %

Test procedure parameters:

The lighting system was subjected to stress as follows:

• Structure-borne noise:approx. 5 to 50 Hz

• Oscillation velocity (Ø): v = 1.8167 mm/s

• Oscillation acceleration (Ø):.....a = 0.6305 m/s²

• Deflection of the system (Ø):......s = 0.0173 mm



Test result/Classification

When operated under the specified test conditions, the recessed luminaire Crono-I Clean 625 TW NL is suitable for use in cleanrooms fulfilling the specifications of the following Air Cleanliness Class according to ISO 14644-1:

Test parameter(s)	Air Cleanliness Class
Structure-borne noise = approx. 5 to 50 Hz	1
Overall result	1

It should be noted that cleanrooms of Class 1 to 5 according to ISO 14644-1 have a higher filter occupancy, which may restrict the use of panel lighting systems. Cleanrooms with a horizontal displacement flow form an exception to this.

The test result may be affected by the surrounding ceiling system, in particular the material pairing between lights and ceiling frames, as well as other mounting accessories. Particle emission behavior should be reassessed in each assembly situation.

The measuring devices used for the qualification tests are calibrated at regular intervals; their results can be traced back to national and international standards. In cases where no national standards exist, the test procedure implemented complies with the technical regulations and norms applicable at the time of the test. The relevant documentation can be viewed on request at any time.

Detailed information and parameters of the test environment can be found in the Fraunhofer IPA test report.

Fraunhofer Institute for Manufacturing Engineering and Automation IPA

Department of Ultraclean Technology and Micromanufacturing

Nobelstrasse 12 70569 Stuttgart Germany

LI 1809-1068

Report No. first document

Report No. current document Place, current date

on behalf of River

Stuttgart, September 25, 2018 Place, date of first document issued

This document only applies to the named product in its original state and is valid for a period of 5 years from the date the first document was issued. The document can be verified under

www.tested-device.com.