

Fraunhofer

TESTED[®] DEVICE

Knauf Ceiling Solutions Hygena Plain

Report No. KN 2409-1561

Statement of Qualification

Single product **Particle Emission**





Statement of Qualification • Single product

Knauf Ceiling Solutions GmbH & Co. KG Customer

> Elsenthal 15 94481 Grafenau Germany

Component tested

Cleanroom Facilities Category:

Wall/Ceiling/Floor/Door Subcategory

Product name: Hygena Plain

(manufacturing date: 1/18/2024; color: white; article number: GR-S-27-02;

size: 1200 x 1200 x 15 mm; grid system: KCS T 24)

Random sampling of particle emissions (airborne) at representative sites under atmospheric conditions

Standards/Guidelines:

Test devices:

Test environment parameters:

Test procedure parameters:

ISO 14644-1, -14

The norms stated generally refer to the version valid at the time of the tests.

Optical particle counter:

LasAir II 110 and LasAir III 110 with measuring ranges $\geq 0.1 \,\mu\text{m}$, $\geq 0.2 \,\mu\text{m}$, \geq 0.3 µm, \geq 0.5 µm, \geq 1.0 µm and \geq 5.0 µm

- Airflow pattern: vertical laminar flow

The ceiling system was subjected to stress as follows:

- Structure-borne noise: approx. 50 Hz
- Oscillation acceleration (Ø):.....a = 1.1737 m/s²
- Deflection of the system (Ø):.....s = 0.1323 mm

Test result/Classification

When operated under the specified test conditions, the ceiling system Hygena Plain is suitable for use in cleanrooms fulfilling the specifications of the following Air Cleanliness Class according to ISO 14644-1:

Test parameter(s)	Air Cleanlines Class
Structure-borne noise = approx. 50 Hz	4
Overall result	

It must be pointed out, that according to ISO 14644-1 cleanrooms classes 1 to 5 have a high filter occupancy, with the result that large-surface ceiling systems cannot be used in some cases. Cleanrooms with a horizontal displacement flow form an exception to this.

The test result may be influenced by the surrounding ceiling system, in particular the material pairing between the light and ceiling frame, as well as other assembly accessories. Particle emission behavior should be re-assessed in the respective assembly situation.

The cut edges/back are made of very porous material. Therefore, the use of the test piece in clean/hygienic areas is considered to be critical.

Please note: Transport damages, incorrect installation, aging behavior, corrosion etc. can influence the test result.

The measuring devices used for the qualification tests are calibrated at regular intervals; their results can be traced back to national and international standards. In cases where no national standards exist, the test procedure implemented complies with the technical regulations and norms applicable at the time of the test. The relevant documentation can be viewed on request at any time.

Detailed information and parameters of the test environment can be found in the Fraunhofer IPA test report.

Fraunhofer Institute for Manufacturing Engineering and Automation IPA

Department of Ultraclean Technology and Micromanufacturing

Nobelstrasse 12 70569 Stuttgart Germany

KN 2409-1561 Report No. first document

Stuttgart, October 2, 2024 Place, date of first document issued

Report No. current document Place, current date

on behalf of RT Buil

This document only applies to the named product in its original state and is valid for a period of 5 years from the date the first document was issued. The document can be verified under

www.tested-device.com

Fraunhofer